Oasis 3-Piece, 60-inch, Ramped Threshold, Roll-In Shower Compartment With ActivLife 3-Bar (2-horizontal / 1-vertical) And Folding Seat Package



Specification – Oasis 3-piece FRP gelcoat shower compartment SH3P-MD-6032, having a ½-inch high maximum finished threshold with floor attachment flange on lower threshold. ActivLife package includes a horizontal bar across the back wall and side wall opposite the seat, a vertical bar on the side wall opposite the seat, a folding seat, and shower curtain rod.

Standards Certification:

The shower compartment listed is manufactured in compliance with ANSI Z124 Standards, and certified through an ongoing, independent quality assurance and testing program.


The factory-applied grab bar and seat package is certified through an independent review program.

NOTE: This model DOES NOT meet the required interior dimensions for ADA Roll-In Shower compliance.



SH3P-MD-6032 R / TLV-LS (RH drain / LH seat / 3-bar package) Model & Package Illustrated **NOTE:** Seat positioning prohibits the installation of a shower enclosure.





Model ID Package Code Description (define configuration referencing drain end)

SH3P-MD-6032 L (left drain) / TLV-RS (right seat) SH3P-MD-6032 R (right drain) / TLV-LS (left seat)

60" x 32", 3-piece, end drain, ramped 1/2-inch threshold shower with ActivLife 1.50" dia. 3-bar and seat package (horizontal back & opposite seat wall bars, vertical bar opposite seat, and folding seat) and shower curtain rod.

Powder Coated Bar Packages (1.25-inch dia.)

SH3P-MD-6032 L (left drain) / TLV-RS WHT (right seat) SH3P-MD-6032 R (right drain) / TLV-LS WHT (left seat)

60" x 32", 3-piece, end drain, ramped 1/2-inch threshold shower with ActivLife 1.25" dia. white powder coated 3-bar and seat package (horizontal back & opposite seat wall bars, vertical bar opposite seat, and folding seat) and shower curtain rod.

SH3P-MD-6032 L (left drain) / TLV-RS OFW (right seat) SH3P-MD-6032 R (right drain) / TLV-LS OFW (left seat)

60" x 32", 3-piece, end drain, ramped 1/2-inch threshold shower with ActivLife 1.25" dia. off-white powder coated 3-bar and seat package (horizontal back & opposite seat wall bars, vertical bar opposite seat, and folding seat) and shower curtain rod.


SH3P-MD-6032 L (left drain) / TLV-RS SNK (right seat) SH3P-MD-6032 R (right drain) / TLV-LS SNK (left seat)


60" x 32", 3-piece, end drain, ramped 1/2-inch threshold shower with ActivLife 1.25" dia. nickel finish 3-bar and seat package (horizontal back & opposite seat wall bars, vertical bar opposite seat, and folding seat) and shower curtain rod.

DELETE / SHWR ROD-SH Delete shower curtain rod from package.

Package Notes:

- 1. Model available without listed package.
- 2. Model available without vertical bar on control side wall, see ActivLife "TL-RS/LS" package code.
- 3. For bar packages without seat, see ActivLife "BP1-60" and "BP2-60" package codes
- 4. For REINFORCEMENT ONLY replicating "TL" package with RH or LH seat reinforcement, see ActivLife "TLRF-RS" or "TLRF-LS" package code.
- 5. For REINFORCEMENT ONLY for horizontal bars (HUD/FHA-Fair Housing), see ActivLife "FH" package code.
- 6. For expanded reinforcement package options, (with or without listed package components), see ActivLife "3SM" and "3SF" package codes.













- Photo 1: Grab Bars: Factory-installed 1.50-inch diameter, concealed attachment, 18 gauge, #304 brushed stainless steel grab bars. Concealed attachment design provides tamper-resistance and minimizes debris collection areas at contact points, compared to common exposed flange bar designs, without compromising bar attachment integrity. (Reinforced areas include a structural core material encapsulated in FRP composite.)
- Photo 2: Grab Bars: Factory-installed 1.25-inch dia. powder coated (in finishes listed above), concealed attachment, 18 gauge, #304 stainless steel grab bars. Concealed attachment design provides tamper-resistance and minimizes debris collection areas at contact points, compared to common exposed flange bar designs, without compromising bar attachment integrity. (Reinforced areas include a structural core material encapsulated in FRP composite.)
- Photo 3: Shower Bench Seat: Factory-installed shower bench seat with non-porous, high-pressure laminate upper and lower surfaces, fused to high-density phenolic core. The seat area secures to an 18 gauge, #304 stainless steel framework, and easily pivots upward to store along the wall without supplemental fasteners. Heavy-duty wall (hinge) bracket design eliminates supplemental legs and is formed from 10 gauge, #304 brushed stainless steel. (Reinforced area includes a structural core material encapsulated in FRP composite.)
- Photo 4: Shower Curtain Rod: Factory-installed 1.00-inch diameter, concealed attachment, 18 gauge, stainless steel shower curtain rod with polished finished.